

DR45M Transilluminator - Parts Checklist

Serial Number

This DR45M transilluminator package contains the following items:

Dark Reader DR45M transilluminator (Electrical: 120 VAC, 60 Hz.)

Amber viewing screen

Pair of viewing glasses

Additional glasses and camera filters (if ordered as separate items)

Be sure to read the Safety & Use Instructions in the accompanying Manual


viewing glasses

Use either the viewing glasses or the amber screen to view sample fluorescence.



amber screen

To view the fluorescence, place the amber screen over the sample. Or alternatively, wear the amber glasses. The amber screen can be used as a camera filter.




sample goes here

fuse
(in rear)

plug

on/off switch



transilluminator

model number and
operating voltage
specification

