

# DR45M Transilluminator - Parts Checklist

Serial Number

This DR45M transilluminator package contains the following items:

Dark Reader DR45M transilluminator (Electrical: 120 VAC, 60 Hz.)

Amber viewing screen

Pair of viewing glasses

Additional glasses and camera filters (if ordered as separate items)

**Be sure to read the Safety & Use Instructions in the accompanying Manual**

## viewing glasses

Use either the viewing glasses or the amber screen to view sample fluorescence.



## amber screen

To view the fluorescence, place the amber screen over the sample. Or alternatively, wear the amber glasses. The amber screen can be used as a camera filter.




sample goes here

fuse  
(in rear)

plug

on/off switch



## transilluminator

model number and  
operating voltage  
specification

